

DSC6021CE1A-00D0

Data Sheet Addendum

Pin Configuration and Description

				Pin Number	Pin Name	Pin Type	Pin Description	
FS		4	VDD	1	FS	Ι	Frequency Select: 1 = Output Frequency 1 0 = Output Frequency 2	
GND		3	Output	2	GND	Power	Power Supply Ground	
				3	Output	О	Oscillator Clock Output	
				4	VDD	Power	Power Supply	

FS Frequencies

Frequency1 (MHz) FS = 1 (Default)	Frequency2 (MHz) FS = 0		
50.0000	80.0000		

Internal pull up on FS pin

Ordering Information

Ordering Part Number	Marking	Temperature Range	Stability	Shipping	Package
DSC6021CE1A-00D0	00D0	-20°C to +70°C	±50ppm	Tube	4-Lead 3.2 x 2.5mm DFN
DSC6021CE1A-00D0T	00D0	-20°C to +70°C	±50ppm	Tape and Reel	4-Lead 3.2 x 2.5mm DFN

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Refer to DSC60XX data sheet for full device specification.

Microchip Technology Inc.

DSC6021CE1A-00D0

http://www.microchip.com