

DSC6021HA3B-01D0

Data Sheet Addendum

Pin Configuration and Description

				Pin Number	Pin Name	Pin Type	Pin Description
FS	FS 1	4	VDD Output	1	FS	Ι	Frequency Select: 1 = Output Frequency 1 0 = Output Frequency 2
GND	2	3		2	GND	Power	Power Supply Ground
	2			3	Output	О	Oscillator Clock Output
				4	VDD	Power	Power Supply

FS Frequencies

Frequency1 (MHz) FS = 1 (Default)	Frequency2 (MHz) FS = 0		
8.0000	10.0000		

Internal pull up on FS pin

Ordering Information

Ordering Part Number	Marking	Temperature Range	Stability	Shipping	Package
DSC6021HA3B-01D0	01D0	-40°C to +125°C	±20ppm	Bag	4-Lead 1.6 x 1.2mm VFLGA
DSC6021HA3B-01D0T	01D0	-40°C to +125°C	±20ppm	Tape and Reel	4-Lead 1.6 x 1.2mm VFLGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Refer to DSC60XX data sheet for full device specification.

Microchip Technology Inc.

DSC6021HA3B-01D0

http://www.microchip.com

Revision 1.0 tcghelp@microchip.com