


DSC6021HE1A-00D7

Data Sheet Addendum

Pin Configuration and Description



Pin Number	Pin Name	Pin Type	Pin Description	
1	FS	I	Frequency Select: 1 = Output Frequency 1 0 = Output Frequency 2	
2	GND	Power	Power Supply Ground	
3	Output	0	Oscillator Clock Output	
4	VDD	Power	Power Supply	

FS Frequencies

Frequency1 (MHz) FS = 1 (Default)	Frequency2 (MHz) FS = 0		
2.0480	4.0960		

Internal pull up on FS pin

Ordering Information

Ordering Part Number	Marking	Temperature Range	Stability	Shipping	Package
DSC6021HE1A-00D7	00D7	-20°C to +70°C	±50ppm	Bag	4-Lead 1.6 x 1.2mm VFLGA
DSC6021HE1A-00D7T	00D7	-20°C to +70°C	±50ppm	Tape and Reel	4-Lead 1.6 x 1.2mm VFLGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Refer to DSC60XX data sheet for full device specification.

Microchip Technology Inc.

http://www.microchip.com

DSC6021HE1A-00D7