

**Pin Configuration and Description**



Pin Number	Pin Name	Pin Type	Pin Description
1	FS	I	Frequency Select: 1 = Output Frequency 1 0 = Output Frequency 2
2	GND	Power	Power Supply Ground
3	Output	O	Oscillator Clock Output
4	VDD	Power	Power Supply

**FS Frequencies**

Frequency1 (MHz) FS = 1 (Default)	Frequency2 (MHz) FS = 0
50.0000	25.0000

Internal pull up on FS pin

**Ordering Information**

Ordering Part Number	Marking	Temperature Range	Stability	Shipping	Package
DSC6021HI2A-009T	009T	-40°C to +85°C	±25ppm	Bag	4-Lead 1.6 x 1.2mm VFLGA
DSC6021HI2A-009TT	009T	-40°C to +85°C	±25ppm	Tape and Reel	4-Lead 1.6 x 1.2mm VFLGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Refer to [DSC60XX data sheet](#) for full device specification.