


DSC6021JE1B-01D7

Data Sheet Addendum

Pin Configuration and Description



Pin Number	Pin Name	Pin Type	Pin Description		
1	FS	I	Frequency Select: 1 = Output Frequency 1 0 = Output Frequency 2		
2	GND	Power	Power Supply Ground		
3	Output	0	Oscillator Clock Output		
4	VDD	Power	Power Supply		

FS Frequencies

Frequency1 (MHz) FS = 1 (Default)	Frequency2 (MHz) FS = 0		
35.8907	59.8178		

Internal pull up on FS pin

Ordering Information

Ordering Part Number	Marking	Temperature Range	Stability	Shipping	Package
DSC6021JE1B-01D7	01D7	-20°C to +70°C	±50ppm	Tube	4-Lead 2.5 x 2.0mm VFLGA
DSC6021JE1B-01D7T	01D7	-20°C to +70°C	±50ppm	Tape and Reel	4-Lead 2.5 x 2.0mm VFLGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Refer to DSC60XX data sheet for full device specification.

Microchip Technology Inc.

http://www.microchip.com

DSC6021JE1B-01D7