


DSC6021JI2A-009S

Data Sheet Addendum

Pin Configuration and Description



Pin Number	Pin Name	Pin Type	Pin Description	
1	FS	I	Frequency Select: 1 = Output Frequency 1 0 = Output Frequency 2	
2	GND	Power	Power Supply Ground	
3	Output	0	Oscillator Clock Output	
4	VDD	Power	Power Supply	

FS Frequencies

Frequency1 (MHz) FS = 1 (Default)	Frequency2 (MHz) FS = 0		
20.0000	25.0000		

Internal pull up on FS pin

Ordering Information

Ordering Part Number	Marking	Temperature Range	Stability	Shipping	Package
DSC6021JI2A-009S	009S	-40°C to +85°C	±25ppm	Tube	4-Lead 2.5 x 2.0mm VFLGA
DSC6021JI2A-009ST	009S	-40°C to +85°C	±25ppm	Tape and Reel	4-Lead 2.5 x 2.0mm VFLGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Refer to DSC60XX data sheet for full device specification.

Microchip Technology Inc. http://www.microchip.com