

DSC6021MI2A-009T

**Data Sheet Addendum** 

## **Pin Configuration and Description**

				Pin Number	Pin Name	Pin Type	Pin Description
FS		4	VDD Output	1	FS	Ι	Frequency Select: 1 = Output Frequency 1 0 = Output Frequency 2
GND		3		2	GND	Power	Power Supply Ground
				3	Output	0	Oscillator Clock Output
				4	VDD	Power	Power Supply

## **FS Frequencies**

Frequency1 (MHz) FS = 1 (Default)	Frequency2 (MHz) FS = 0		
50.0000	25.0000		

Internal pull up on FS pin

## **Ordering Information**

Ordering Part Number	Marking	Temperature Range	Stability	Shipping	Package
DSC6021MI2A-009T	009T	$-40^{\circ}$ C to $+85^{\circ}$ C	±25ppm	Bag	4-Lead 2.0 x 1.6mm VFLGA
DSC6021MI2A-009TT	009T	$-40^{\circ}$ C to $+85^{\circ}$ C	±25ppm	Tape and Reel	4-Lead 2.0 x 1.6mm VFLGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Refer to DSC60XX data sheet for full device specification.

Microchip Technology Inc.

http://www.microchip.com

DSC6021MI2A-009T