

DSC6023JE1B-01D8

Data Sheet Addendum

Pin Configuration and Description

				Pin Number	Pin Name	Pin Type	Pin Description
FS	1	4	VDD Output	1	FS	Ι	Frequency Select: 1 = Output Frequency 1 0 = Output Frequency 2
				2	GND	Power	Power Supply Ground
GND	2	3		3	Output	О	Oscillator Clock Output Low Drive
				4	VDD	Power	Power Supply

FS Frequencies

Frequency1 (MHz) FS = 1 (Default)	Frequency2 (MHz) FS = 0		
35.8907	44.8634		

Internal pull up on FS pin

Ordering Information

Ordering Part Number	Marking	Temperature Range	Stability	Shipping	Package
DSC6023JE1B-01D8	01D8	$-20^{\circ}C$ to $+70^{\circ}C$	±50ppm	Tube	4-Lead 2.5 x 2.0mm VFLGA
DSC6023JE1B-01D8T	01D8	$-20^{\circ}C$ to $+70^{\circ}C$	±50ppm	Tape and Reel	4-Lead 2.5 x 2.0mm VFLGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Refer to DSC60XX data sheet for full device specification.

Microchip Technology Inc.

http://www.microchip.com

DSC6023JE1B-01D8

Revision 1.0 tcghelp@microchip.com