# DSC2311KM2-R0050



## Crystal-less<sup>TM</sup> Configurable Clock Generator

## **General Description**

DSC2311KM2-R0050 is a crystal-less clock generator that is factory configurable to simultaneously output two separate frequencies from 2.3 to 170MHz. The generator uses proven silicon technology to provide low jitter and high frequency stability across a wide range of supply voltages and temperatures. By eliminating the external quartz crystal, crystal-less clock generators significantly enhance reliability and accelerate product development, while meeting stringent clock performance criteria for a variety of consumer electronics, communications, and storage applications.

DSC2311KM2-R0050 has an output enable/disable feature allowing it to disable the outputs when OE is low. The device is available in a space-saving 6-pin 2.5mm x 2.0mm TDFN package that needs only a single external bypass capacitor. This requires a PCB footprint equivalent to that of a 1.0mm x 1.0mm crystal-based clock generator.


# **Applications**

- Consumer Electronics
- Camera and Imaging Modules
- Home Automation
- Industrial and Power Conversion
- Mobile Communications, Internet, and Sensor Devices
- · Solid State, Hard Drive, and Flash Drive Storage
- Automotive

### **Features**

- Two simultaneous LVCMOS outputs:
  - 24MHz
  - 38.4MHz
- Low RMS phase jitter: <1ps (typical)
- ±25ppm frequency stability
- -55°C to +125°C automotive temperature range
- High supply noise rejection: -50dBc
- High shock & vibration immunity
  - Qualified to MIL-STD-883
- High reliability
- 20x higher MTBF than crystal-based clock generator designs
- Programmable output strength for EMI reduction and signal integrity optimization
- Supply range of 2.25 to 3.6V
- AEC-Q100 automotive qualified
- 6-pin 2.5mm x 2.0mm TDFN package

### **Block Diagram**



ClockWorks is a registered trademark of Microchip Technology Inc.

Microchip Technology Inc.


http://www.microchip.com

# **Ordering Information**

Ordering Part Number	Industrial Temperature Range	Shipping	Package
DSC2311KM2-R0050	-55°C to +125°C	Tube	6-pin 2.5mm x 2.0mm TDFN
DSC2311KM2-R0050T	-55°C to +125°C	Tape and Reel	6-pin 2.5mm x 2.0mm TDFN

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

# **Pin Configuration**



6-pin 2.5mm x 2.0mm TDFN

# **Pin Description**

Pin Number	Pin Name	Pin Type	Pin Level	Pin Function
1	OE	I		Active high output enable for CLK0 and CLK1
2	DNC			Leave unconnected or connect to the ground
3	GND	PWR		Power supply ground
4	CLK0	0	LVCMOS	CLK0 output frequency = 24MHz
5	CLK1	0	LVCMOS	CLK1 output frequency = 38.4MHz
6	VDD	PWR		Power supply

### **Specifications** (Unless specified otherwise: $T = 25^{\circ}C$ , VDD = 3.3V)

Parameter	Symbol	Condition	Min.	Тур.	Max.	Units
Supply Voltage <sup>1</sup>	VDD		2.25		3.6	V
Supply Current <sup>2</sup>	IDD	OE pin low - outputs are disabled		21	23	mA
Frequency Stability <sup>6</sup>	ΔF	Includes frequency variation due to initial tolerance, temp. and power supply voltage		±25		ppm
Aging	ΔF	First year (@ 25°C)			±5	ppm
Startup Time <sup>3</sup>	tSU	T = 25°C			5	ms
Input Logic High Input Logic Low	VIH VIL		0.75 x VDD		0.25 x VDD	V
Output Disable Time <sup>4</sup>	tDA				5	ns
Output Enable Time <sup>4</sup>	tEN				20	ns
Pull-Up Resistor <sup>2</sup>		Pull-up exists on pin 1		40		kOhms
Output Logic High Output Logic Low	VOH VOL	$I = \pm 6mA$	0.9 x VDD -		- 0.1 x VDD	V
Output Transition Time <sup>4</sup> Rise Time Fall Time	tR tF	20% to 80% CL = 15pF		1.1 1.43	2 2	ns
Frequency	F0 F1	CLK0 CLK1		24 38.4		MHz
Output Duty Cycle	SYM		45		55	%
Period Jitter <sup>5</sup>	JPER	CLK0 = CLK1 = 25MHz		3		psRMS
Integrated Phase Noise	JCC	200kHz to 20MHz @ 25MHz 100kHz to 20MHz @ 25MHz 12kHz to 20MHz @ 25MHz		0.3 0.38 1.7	2	psRMS

#### Notes:

- 1. Pin 4 VDD should be filtered with 0.1uF capacitor.
- 2. Output is enabled if OE pad is high or not connected. Supply current = Disabled Current +  $\Delta$ IDD from CLK1. See Current Consumption graph on next page.
- 3. tSU is time to stable output frequency after VDD is applied and outputs are enabled.
- 4. See Figure 3 for detail (all based on maximum drive settings).
- 5. Period Jitter includes crosstalk from adjacent output.
- $6.\ For\ other\ ppm\ stabilities,\ contact\ the\ factory\ at\ MEMS\_Support@microchip.com.$

# **Absolute Maximum Ratings**

Item	Min.	Max.	Units	Condition
Supply Voltage	-0.3	+4.0	V	
Input Voltage	-0.3	VDD + 0.3	V	
Junction Temp	-	+150	°C	
Storage Temp	-55	+150	°C	
Soldering Temp	-	+260	°C	40sec max.
ESD HBM MM CDM	-	4000 400 1500	V	

# **Current Consumption**




Figure 1. Total Current = Disabled Current +  $\triangle$ IDD Fout1 +  $\triangle$ IDD Fout2

# **Solder Reflow Profile**




Figure 2. Solder Reflow Profile

6 QFN MSL 1 @ 260°C refer to JSTD-020C			
Ramp-Up Rate (200°C to Peak Temp)	3°C/sec Max.		
Preheat Time 150°C to 200°C	60 - 180 sec		
Time maintained above 217°C	60 - 150 sec		
Peak Temperature	255 - 260°C		
Time within 5°C of actual Peak	20 - 40 sec		
Ramp-Down Rate	6°C/sec Max.		
Time 25°C to Peak Temperature	8 min Max.		

# **OE Function and Output Waveform**





Figure 3. OE Function and Output Waveform

# Package Information<sup>7</sup>



6-pin TDFN (2.5mm x 2.0mm)

#### Note:

7. Package information is correct as of the publication date. For updates and most current information, go to www.microchip.com.

Microchip makes no representations or warranties with respect to the accuracy or completeness of the information furnished in this data sheet. This information is not intended as a warranty and Microchip does not assume responsibility for its use. Microchip reserves the right to change circuitry, specifications and descriptions at any time without notice. No license, whether express, implied, arising by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Microchip's terms and conditions of sale for such products, Microchip assumes no liability whatsoever, and Microchip disclaims any express or implied warranty relating to the sale and/or use of Microchip products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right.

Microchip products are not designed or authorized for use as components in life support appliances, devices or systems where malfunction of a product can reasonably be expected to result in personal injury. Life support devices or systems are devices or systems that (a) are intended for surgical implant into the body or (b) support or sustain life, and whose failure to perform can be reasonably expected to result in a significant injury to the user. A Purchaser's use or sale of Microchip Products for use in life support appliances, devices or systems is a Purchaser's own risk and Purchaser agrees to fully indemnify Microchip for any damages resulting from such use or sale.

© 2016 Microchip Technology Inc.