

## DSC6021CE1A-00CW

**Data Sheet Addendum** 

## **Pin Configuration and Description**

				Pin Number	Pin Name	Pin Type	Pin Description
FS	1	4	VDD Output	1	FS	Ι	Frequency Select: 1 = Output Frequency 1 0 = Output Frequency 2
GND	2	3		2	GND	Power	Power Supply Ground
				3	Output	0	Oscillator Clock Output
				4	VDD	Power	Power Supply

## **FS Frequencies**

Frequency1 (MHz) FS = 1 (Default)	Frequency2 (MHz) FS = 0		
60.0000	70.0000		

Internal pull up on FS pin

## **Ordering Information**

Ordering Part Number	Marking	Temperature Range	Stability	Shipping	Package
DSC6021CE1A-00CW	00CW	-20°C to +70°C	±50ppm	Tube	4-Lead 3.2 x 2.5mm DFN
DSC6021CE1A-00CWT	00CW	-20°C to +70°C	±50ppm	Tape and Reel	4-Lead 3.2 x 2.5mm DFN

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Refer to DSC60XX data sheet for full device specification.

Microchip Technology Inc.

DSC6021CE1A-00CW

http://www.microchip.com

Revision 1.0 tcghelp@microchip.com