MICROCHIP

MX553BHA156M250

Ultra-Low Jitter 156.25MHz LVPECL XO

ClockWorks® FUSION

General Description

The MX553BHA156M250 is an ultra-low phase jitter XO with LVPECL output optimized for high line rate applications.

Applications

- 10/40/400 Gigabit Ethernet
- Fibre Channel 10G/12G SERDES

Absolute Maximum Ratings1

Supply Voltage (VIN)	+4.6V
Lead Temperature (soldering, 10s)	260°C
Case Temperature	115°C
Storage Temperature (T _a)	65°C to +125°C
Storage Temperature (T _S) ESD Machine Model	200V
ESD Rating (HBM)	2kV

Features

- 156.25MHz LVPECL
- Typical phase noise:
 - 104fs (Integration range: 1.875MHz-20MHz)
- ±20ppm total frequency stability
- -10°C to +75°C temperature range
- Industry standard 6-Pin 5mm x 3.2mm LGA package

Operating Ratings²

Supply Voltage (VIN)	+2.375V to $+3.63V$
Ambient Temperature (TA)	10° C to +75°C
Junction Thermal Resistance	
LGA (T _{IC}) Still Air	58°C/W
` JC ′	

Electrical Characteristics

VDD = 2.375 - 3.63V, TA = -10°C to +75°C, outputs terminated with 50Ω to VDD - 2V.³

Symbol	Parameter	Condition	Min.	Тур.	Max.	Units
IDD	Supply Current				120	mA
F0	Center Frequency			156.25		MHz
	Frequency Stability	Note 4			±20	ppm
Øj	Phase Noise	Integration Range (12kHz to 20MHz) Integration Range (1.875MHz to 20MHz)		154 104		fsRMS
Tstart	Start-Up Time				20	ms
TR/TF	Rise/Fall time		85		350	ps
	Duty Cycle		45		55	%
VOH	Output High Voltage	LVPECL output levels	VDD - 1.35	VDD - 1.01	VDD - 0.8	V
VOL	Output Low Voltage	LVPECL output levels	VDD - 2.0	VDD - 1.78	VDD - 1.6	V
Vswing	Peak to Peak Output Voltage Swing		0.65	0.77	0.95	V

Notes

- 1. Exceeding the absolute maximum ratings may damage the device.
- 2. The device is not guaranteed to function outside its operating ratings.
- ${\it 3. Guaranteed \ after \ thermal \ equilibrium.}$
- 4. Inclusive of initial accuracy, supply voltage, temperature drift, aging (5yrs), shock, vibration.

ClockWorks is a registered trademark of Microchip Technology Inc.

Microchip Technology Inc. http://www.microchip.com


March 02, 2023 MX553BH1-2279 Revision 1.0 tcghelp@microchip.com

Ordering Information

Ordering Part Number	Marking Line 1	Marking Line 3	Shipping	Package
MX553BHA156M250	MX553B	HA1562	Tube	6-Pin 5mm x 3.2mm LGA
MX553BHA156M250-TR	MX553B	HA1562	Tape and Reel	6-Pin 5mm x 3.2mm LGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Pin Configuration



Pin Description

Pin Number	Pin Name	Pin Type	Pin Level	Pin Function
1	OE	I, SE	LVCMOS	Output Enable, disables output to tri-state, $0 = Disabled, 1 = Enabled, 50k\Omega$ Pull-Up (Internal)
2	DNC			Make no connection, leave floating.
3	GND	PWR		Power Supply Ground
4, 5	Q, /Q	O, Diff	LVPECL	Clock Output Frequency = 156.25MHz
6	VDD	PWR		Power Supply

Environmental Specifications

Thermal Shock	MIL-STD-883, Method 1011, Condition A	
Moisture Resistance	MIL-STD-883, Method 1004	
Mechanical Shock	MIL-STD-883, Method 2002, Condition C	
Mechanical Vibration	MIL-STD-883, Method 2007, Condition B	
Resistance to Soldering Heat	J-STD-020C, Table 5-2 Pb-free devices (except 2 cycles max)	
Hazardous Substance	Pb-Free / RoHS / Green Compliant	
Solderability	JESD22-B102-D Method 2 (Preconditioning E)	
Terminal Strength	MIL-STD-883, Method 2004, Test Condition D	
Gross Leak	MIL-STD-883, Method 1014, Condition C	
Fine Leak	MIL-STD-883, Method 1014, Condition A2, R1=2x10-8 atm cc/s	
MSL Level	Crystal - MSL-1, Package MSL-3	
Solvent Resistance	MIL-STD-202, Method 215	




Figure 1. LVPECL Output 156.25MHz 1.875MHz-20MHz 104fs





Figure 2. LVPECL Output 156.25MHz 12kHz-20MHz 154fs

Package Information and Recommended Land Pattern for 6-Pin LGA³



Note:

3. Package information is correct as of the publication date. For updates and most current information, go to www.microchip.com.

Microchip Technology Inc.

http://www.microchip.com

Microchip makes no representations or warranties with respect to the accuracy or completeness of the information furnished in this data sheet. This information is not intended as a warranty and Microchip does not assume responsibility for its use. Microchip reserves the right to change circuitry, specifications and descriptions at any time without notice. No license, whether express, implied, arising by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Microchip's terms and conditions of sale for such products, Microchip assumes no liability whatsoever, and Microchip disclaims any express or implied warranty relating to the sale and/or use of Microchip products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right.

© 2023 Microchip Technology Inc.