

MX574EBC16M0000

Ultra-Low Jitter 16MHz LVCMOS XO

ClockWorks® FUSION

General Description

The MX574EBC16M0000 is an ultra-low phase jitter XO with LVCMOS output optimized for high line rate applications.

Features

- 16MHz LVCMOS
- Typical phase noise:
 - 100fs (Integration range: 1.875MHz-20MHz)
- ±50ppm total frequency stability
- -40°C to +85°C temperature range
- Industry standard 6-Pin 7mm x 5mm LGA package

Absolute Maximum Ratings¹

Supply Voltage (VIN)	+4.6V
Lead Temperature (soldering, 10s)	260°C
Case Temperature	115°C
Storage Temperature (T _a)	65°C to +125°C
Storage Temperature (T _s) ESD Machine Model	200V
ESD Rating (HBM)	2kV

Electrical Characteristics

VDD = 2.375 - 3.63V, TA = $-40^{\circ}C$ to $+85^{\circ}C$, output terminated with 50 Ohms to VDD/2.3

Symbol	Parameter	Condition	Min.	Тур.	Max.	Units
IDD	Supply Current				95	mA
F0	Center Frequency			16		MHz
	Frequency Stability	Note 4			±50	ppm
Øj	Phase Noise	Integration Range (12kHz to 20MHz) Integration Range (1.875MHz to 20MHz)		220 100		fsRMS
Tstart	Start-Up Time				20	ms
TR/TF	Rise/Fall time		100		500	ps
	Duty Cycle		45		55	%
VIH	Input High Voltage	3.3V Operation	2		VDD + 0.3	v
VIL	Input Low Voltage	3.3V Operation	-0.3		0.8	v
VOH	Output High Voltage	LVCMOS output levels	VDD - 0.8			v
VOL	Output Low Voltage	LVCMOS output levels			0.6	V

Notes:

1. Exceeding the absolute maximum ratings may damage the device.

2. The device is not guaranteed to function outside its operating ratings.

3. Guaranteed after thermal equilibrium.

4. Inclusive of initial accuracy, temperature drift, aging, shock, vibration.

ClockWorks is a registered trademark of Microchip Technology Inc.

Microchip Technology Inc.

July 04, 2020 MX574EB1-9118 http://www.microchip.com

Revision 1.0 tcghelp@microchip.com

Operating Ratings²


Supply Voltage (VIN)	+2.375V to +3.63V
Ambient Temperature (TA)	40°C to +85°C
Junction Thermal Resistance	
LGA (T _{IC}) Still Air	53°C/W

Ordering Information

Ordering Part Number	Marking Line 1	Marking Line 3	Shipping	Package
MX574EBC16M0000	MX574EB	C16M0000	Tube	6-Pin 7mm x 5mm LGA
MX574EBC16M0000-TR	MX574EB	C16M0000	Tape and Reel	6-Pin 7mm x 5mm LGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Pin Configuration




Pin Description

Pin Number	Pin Name	Pin Type	Pin Level	Pin Function
1	OE	I, SE	LVCMOS	Output Enable, disables output to tri-state, 0 = Disabled, 1 = Enabled, 50k Ohms Pull-Up (Internal)
2	DNC			Make no connection, leave floating.
3	GND	PWR		Power Supply Ground
4, 5	Q, DNC	O, SE	LVCMOS	Clock Output Frequency = 16MHz
6	VDD	PWR		Power Supply

Environmental Specifications

Thermal Shock	MIL-STD-883, Method 1011, Condition A	
Moisture Resistance	MIL-STD-883, Method 1004	
Mechanical Shock	MIL-STD-883, Method 2002, Condition C	
Mechanical Vibration	MIL-STD-883, Method 2007, Condition A	
Resistance to Soldering Heat	J-STD-020C, Table 5-2 Pb-free devices (except 2 cycles max)	
Hazardous Substance	Pb-Free / RoHS / Green Compliant	
Solderability	JESD22-B102-D Method 2 (Preconditioning E)	
Terminal Strength	MIL-STD-883, Method 2004, Test Condition D	
Gross Leak	MIL-STD-883, Method 1014, Condition C	
Fine Leak	MIL-STD-883, Method 1014, Condition A2, R1=2x10-8 atm cc/s	
MSL Level	Crystal - MSL-1, Package MSL-3	
Solvent Resistance	MIL-STD-202, Method 215	

Package Information and Recommended Land Pattern for 6-Pin LGA³



Microchip Technology Inc.

http://www.microchip.com

Microchip makes no representations or warranties with respect to the accuracy or completeness of the information furnished in this data sheet. This information is not intended as a warranty and Microchip does not assume responsibility for its use. Microchip reserves the right to change circuitry, specifications and descriptions at any time without notice. No license, whether express, implied, arising by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Microchip's terms and conditions of sale for such products, Microchip assumes no liability whatsoever, and Microchip disclaims any express or implied warranty relating to the sale and/or use of Microchip products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right.

© 2020 Microchip Technology Inc.