

MX553ENL125M000

Ultra-Low Jitter 125MHz LVPECL XO

ClockWorks® FUSION

- 115fs (Integration range: 1.875MHz-20MHz)

• Industry standard 6-Pin 5mm x 3.2mm LGA

Supply Voltage (VIN).....+2.375V to +3.63V Ambient Temperature (TA)....-40°C to +85°C

LGA (T_{IA}) Still Air.....58°C/W

Features

package

• 125MHz LVPECL

• Typical phase noise:

Operating Ratings²

Junction Thermal Resistance

• ± 50 ppm total frequency stability

• -40° C to $+85^{\circ}$ C temperature range

General Description

The MX553ENL125M000 is an ultra-low phase jitter XO with LVPECL output optimized for high line rate applications.

Applications

- Gigabit Ethernet
- Storage

Absolute Maximum Ratings¹

Supply Voltage (VIN)	+4.6V
Lead Temperature (soldering, 10s)	
Case Temperature	115°C
Storage Temperature (T _S) ESD Machine Model	65°C to +125°C
ESD Machine Model	200V
ESD Rating (HBM)	2kV

Electrical Characteristics

VDD = 2.375 - 3.63V, TA = $-40^{\circ}C$ to $+85^{\circ}C$, outputs terminated with 50 Ohms to VDD - $2V.^{3}$

Symbol	Parameter	Condition	Min.	Тур.	Max.	Units
IDD	Supply Current				120	mA
F0	Center Frequency			125		MHz
	Frequency Stability	Note 4			±50	ppm
Øj	Phase Noise	Integration Range (12kHz to 20MHz) Integration Range (1.875MHz to 20MHz)		159 115		fsRMS
Tstart	Start-Up Time				20	ms
TR/TF	Rise/Fall time		85		350	ps
	Duty Cycle		45		55	%
VOH	Output High Voltage	LVPECL output levels	VDD - 1.35	VDD - 1.01	VDD - 0.8	V
VOL	Output Low Voltage	LVPECL output levels	VDD - 2.0	VDD - 1.78	VDD - 1.6	V
Vswing	Peak to Peak Output Voltage Swing		0.65	0.77	0.95	v

Notes:

1. Exceeding the absolute maximum ratings may damage the device.

2. The device is not guaranteed to function outside its operating ratings.

3. Guaranteed after thermal equilibrium.

4. Inclusive of initial accuracy, temperature drift, aging, shock, vibration.

ClockWorks is a registered trademark of Microchip Technology Inc.

Microchip Technology Inc.

January 02, 2019 MX553EN2-5430 http://www.microchip.com


Revision 1.0 tcghelp@microchip.com

Ordering Information

Ordering Part Number	Marking Line 1	Marking Line 3	Shipping	Package
MX553ENL125M000	MX553E	NL1250	Tube	6-Pin 5mm x 3.2mm LGA
MX553ENL125M000-TR	MX553E	NL1250	Tape and Reel	6-Pin 5mm x 3.2mm LGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Pin Configuration



Pin Description

Pin Number	Pin Name	Pin Type	Pin Level	Pin Function
1	DNC			Make no connection, leave floating.
2	OE	I, SE	LVCMOS	Output Enable, disables output to tri-state, 1 = Disabled, 0 = Enabled, 50k Ohms Pull-Down (Internal)
3	GND	PWR		Power Supply Ground
4, 5	Q, /Q	O, Diff	LVPECL	Clock Output Frequency = 125MHz
6	VDD	PWR		Power Supply

Environmental Specifications

MIL-STD-883, Method 1011, Condition A	
MIL-STD-883, Method 1004	
MIL-STD-883, Method 2002, Condition E	
MIL-STD-883, Method 2007, Condition C	
J-STD-020C, Table 5-2 Pb-free devices (except 2 cycles max)	
Pb-Free / RoHS / Green Compliant	
JESD22-B102-D Method 2 (Preconditioning E)	
MIL-STD-883, Method 2004, Test Condition D	
MIL-STD-883, Method 1014, Condition C	
MIL-STD-883, Method 1014, Condition A2, R1=2x10-8 atm cc/s	
MIL-STD-202, Method 215	




Figure 1. LVPECL Output 125MHz 1.875MHz-20MHz 115fs





Figure 2. LVPECL Output 125MHz 12kHz-20MHz 159fs

Package Information and Recommended Land Pattern for 6-Pin LGA³



Microchip Technology Inc.

http://www.microchip.com

Microchip makes no representations or warranties with respect to the accuracy or completeness of the information furnished in this data sheet. This information is not intended as a warranty and Microchip does not assume responsibility for its use. Microchip reserves the right to change circuitry, specifications and descriptions at any time without notice. No license, whether express, implied, arising by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Microchip's terms and conditions of sale for such products, Microchip assumes no liability whatsoever, and Microchip disclaims any express or implied warranty relating to the sale and/or use of Microchip products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right.

© 2019 Microchip Technology Inc.

Note: