

MX575ABH50M0000

Ultra-Low Jitter 50MHz LVCMOS XO

ClockWorks® FUSION

General Description

The MX575ABH50M0000 is an ultra-low phase jitter XO with LVCMOS output optimized for high line rate applications.

Features

- 50MHz LVCMOS
- Typical phase noise:
 - 100fs (Integration range: 1.875MHz-20MHz)
- ±50ppm total frequency stability
- -40°C to +85°C temperature range
- Industry standard 6-Pin 7mm x 5mm LGA package

Absolute Maximum Ratings

Supply Voltage (VIN)	+4.6V
Lead Temperature (soldering, 10s)	260°C
Storage Temperature (T _s)	125°C
ESD Rating (HBM)	

Electrical Characteristics

VDD = 2.375 - 3.63V, TA = $-40^{\circ}C$ to $+85^{\circ}C$, output terminated with 50 Ohms to VDD/ $2.^{1}$

Units Symbol Parameter Condition Min. Typ. Max. IDD Supply Current 95 mA F0 Center Frequency 50 MHz Frequency Stability ±50 Note 2 ppm Integration Range (12kHz to 20MHz) 142 Øj Phase Noise fsRMS Integration Range (1.875MHz to 20MHz) 100 Start-Up Time Tstart 20ms TR/TF Rise/Fall time 100 500 ps 45 Duty Cycle 55 % 2 VIH V Input High Voltage 3.3V Operation VDD + 0.3VIL Input Low Voltage 3.3V Operation -0.3 0.8 V VOH Output High Voltage LVCMOS output levels VDD - 0.8 V VOL Output Low Voltage LVCMOS output levels 0.6 V

Notes:

1. Guaranteed after thermal equilibrium.

2. Inclusive of initial accuracy, temperature drift, aging, shock, vibration.

ClockWorks is a registered trademark of Microchip Technology Inc.

Microchip Technology Inc.

November 23, 2016 MX575AB1-4571 http://www.microchip.com

Revision 1.0 tcghelp@microchip.com

Operating Ratings


Supply Voltage (VIN).....+2.375V to +3.63V Ambient Temperature (TA)....-40°C to +85°C

Ordering Information

Ordering Part Number	Marking Line 1	Marking Line 3	Shipping	Package
MX575ABH50M0000	MX575AB	H50M0000	Tube	6-Pin 7mm x 5mm LGA
MX575ABH50M0000 TR	MX575AB	H50M0000	Tape and Reel	6-Pin 7mm x 5mm LGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Pin Configuration



Pin Description

Pin Number	Pin Name	Pin Type	Pin Level	Pin Function
1	OE	I, SE	LVCMOS	Output Enable, disables output to tri-state, 1 = Disabled, 0 = Enabled, 50k Ohms Pull-Down
2	DNC			Make no connection, leave floating.
3	GND	PWR		Power Supply Ground
4, 5	Q, DNC	O, SE	LVCMOS	Clock Output Frequency = 50MHz
6	VDD	PWR		Power Supply





Figure 1. LVCMOS Output 50MHz 12kHz-20MHz 142fs

Package Information and Recommended Land Pattern for 6-Pin LGA³



Microchip Technology Inc.

http://www.microchip.com

Microchip makes no representations or warranties with respect to the accuracy or completeness of the information furnished in this data sheet. This information is not intended as a warranty and Microchip does not assume responsibility for its use. Microchip reserves the right to change circuitry, specifications and descriptions at any time without notice. No license, whether express, implied, arising by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Microchip's terms and conditions of sale for such products, Microchip assumes no liability whatsoever, and Microchip disclaims any express or implied warranty relating to the sale and/or use of Microchip products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right.

© 2016 Microchip Technology Inc.