

# MX575ANN25M0000

#### Ultra-Low Jitter 25MHz LVCMOS XO

#### ClockWorks® FUSION

### **General Description**

The MX575ANN25M0000 is an ultra-low phase jitter XO with LVCMOS output optimized for high line rate applications.

#### Features

- 25MHz LVCMOS
- Typical phase noise:
  - 77fs (Integration range: 1.875MHz-5MHz)
- ±50ppm total frequency stability
- $-40^{\circ}$ C to  $+85^{\circ}$ C temperature range
- Industry standard 6-Pin 7mm x 5mm LGA package

### Absolute Maximum Ratings<sup>1</sup>

Supply Voltage (VIN)	+4.6V
Lead Temperature (soldering, 10s)	260°C
Case Temperature	115°C
Storage Temperature (T <sub>a</sub> )	65°C to +125°C
Storage Temperature (T <sub>s</sub> ) ESD Machine Model	200V
ESD Rating (HBM)	2kV

## **Electrical Characteristics**

VDD = 2.375 - 3.63V, TA =  $-40^{\circ}C$  to  $+85^{\circ}C$ , output terminated with 50 Ohms to VDD/2.3

Symbol	Parameter	Condition	Min.	Тур.	Max.	Units
IDD	Supply Current				95	mA
F0 Center Frequency				25		MHz
	Frequency Stability	Note 4			±50	ppm
Øj	Phase Noise	Integration Range (12kHz to 5MHz) Integration Range (1.875MHz to 5MHz)		131 77		fsRMS
Tstart	Start-Up Time				20	ms
TR/TF	Rise/Fall time		100		500	ps
	Duty Cycle		45		55	%
VIH	Input High Voltage	3.3V Operation	2		VDD + 0.3	V
VIL	Input Low Voltage	3.3V Operation	-0.3		0.8	V
VOH	Output High Voltage	LVCMOS output levels	VDD - 0.8			V
VOL	Output Low Voltage	LVCMOS output levels			0.6	v

Notes:

1. Exceeding the absolute maximum ratings may damage the device.

2. The device is not guaranteed to function outside its operating ratings.

3. Guaranteed after thermal equilibrium.

4. Inclusive of initial accuracy, temperature drift, aging, shock, vibration.

ClockWorks is a registered trademark of Microchip Technology Inc.

Microchip Technology Inc.

October 03, 2019 MX575AN2-8328 http://www.microchip.com

Revision 1.0 tcghelp@microchip.com

# **Operating Ratings<sup>2</sup>**


Supply Voltage (VIN)	+2.375V to +3.63V
Ambient Temperature (TA)	$-40^{\circ}$ C to $+85^{\circ}$ C
Junction Thermal Resistance	
LGA (T <sub>IA</sub> ) Still Air	53°C/W
JA	

## **Ordering Information**

Ordering Part Number	Marking Line 1	Marking Line 3	Shipping	Package
MX575ANN25M0000	MX575AN	N25M0000	Tube	6-Pin 7mm x 5mm LGA
MX575ANN25M0000-TR	MX575AN	N25M0000	Tape and Reel	6-Pin 7mm x 5mm LGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

## **Pin Configuration**





# **Pin Description**

Pin Number	Pin Name	Pin Type	Pin Level	Pin Function
1	DNC			Make no connection, leave floating.
2	OE	I, SE	LVCMOS	Output Enable, disables output to tri-state, 1 = Disabled, 0 = Enabled, 50k Ohms Pull-Down (Internal)
3	GND	PWR		Power Supply Ground
4, 5	Q, DNC	O, SE	LVCMOS	Clock Output Frequency = 25MHz
6	VDD	PWR		Power Supply

# **Environmental Specifications**

MIL-STD-883, Method 1011, Condition A	
MIL-STD-883, Method 1004	
MIL-STD-883, Method 2002, Condition E	
MIL-STD-883, Method 2007, Condition C	
J-STD-020C, Table 5-2 Pb-free devices (except 2 cycles max)	
Pb-Free / RoHS / Green Compliant	
JESD22-B102-D Method 2 (Preconditioning E)	
MIL-STD-883, Method 2004, Test Condition D	
MIL-STD-883, Method 1014, Condition C	
MIL-STD-883, Method 1014, Condition A2, R1=2x10-8 atm cc/s	
MIL-STD-202, Method 215	









Figure 2. LVCMOS Output 25MHz 12kHz-5MHz 131fs

## Package Information and Recommended Land Pattern for 6-Pin LGA<sup>3</sup>



#### Microchip Technology Inc.

#### http://www.microchip.com

Microchip makes no representations or warranties with respect to the accuracy or completeness of the information furnished in this data sheet. This information is not intended as a warranty and Microchip does not assume responsibility for its use. Microchip reserves the right to change circuitry, specifications and descriptions at any time without notice. No license, whether express, implied, arising by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Microchip's terms and conditions of sale for such products, Microchip assumes no liability whatsoever, and Microchip disclaims any express or implied warranty relating to the sale and/or use of Microchip products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right.

© 2019 Microchip Technology Inc.