MICROCHIP

MX775ABA156M250

Ultra-Low Jitter 156.25MHz LVPECL XO

with Integrated Quartz Crystal

General Description

The MX775ABA156M250 is an ultra-low phase jitter XO with LVPECL output optimized for high line rate applications.

Applications

- 10/40/400 Gigabit Ethernet
- Fibre Channel 10G/12G SERDES

Absolute Maximum Ratings¹

Supply Voltage (VDD)	+4.6V
Input Voltage (VIN)	0.50V to VDD +4.6V
ESD Protection (HBM)	2kV
ESD Protection (MM)	200V

Features

- 156.25MHz LVPECL
- Typical phase noise:
 - 85fs (Integration range: 12kHz-20MHz)
- ±50ppm total frequency stability
- -40°C to +85°C temperature range
- Standard 6-Pin 7mm x 5mm LGA package
- Both the package and the crystal are MSL-1

Operating Ratings²

Supply Voltage (VDD)	+2.375V to +3.465V
Junction Thermal Resistance	
$LGA(\theta_{IA})$	52.8°C/W

Electrical Characteristics

VDD = $3.3V \pm 5\%$ to $2.5V \pm 5\%$, TA = -40° C to $+85^{\circ}$ C, unless otherwise noted. RL = 50Ω to VDD - 2V.

Parameter	Symbol	Min.	Тур.	Max.	Units	Condition	
Supply Voltage	VDD	2.375	2.5	2.625	V	2.5V Operation	
Supply Voltage	100	3.135	3.3	3.465	•	3.3V Operation	
Current Consumption	IDD	-	135	180	mA	@3.3V	
Frequency Stability				±50	ppm	Note 4	
Output High Voltage	VOH	VDDO - 1.35	VDDO - 1.01	VDDO - 0.8	V	50Ω to VDDO - 2V	
Output Low Voltage	VOL	VDDO - 2	VDDO - 1.78	VDDO - 1.6	V	50Ω to VDDO - 2V	
Peak-to-Peak Output	VSWING	0.65	0.77	0.95	V		
Voltage	7577110	0.03	0.77	0.73	,		
Output Rise/Fall Time	tR/tF	85	135	350	ps	LVPECL output	
Outroot Duto Cools	ODC	45	50	55	%	All output frequencies	
Output Duty Cycle	ODC	48	50	52	%0	< 450MHz output frequencies	
PLL Lock Time	TLOCK	-	5	20	ms	Time from 90% VDD	
RMS Phase Jitter ³	tJIT(Ø)	-	85	-	fs	156.25MHz, Integration range (12kHz-20MHz)	

Notes:

- 1. Exceeding the absolute maximum ratings may damage the device.
- 2. The device is not guaranteed to function outside its operating ratings.
- 3. All phase noise measurements were taken with an Agilent 5052B phase noise system.
- 4. Inclusive of initial accuracy, temperature drift, aging, shock, vibration.

ClockWorks is a registered trademark of Microchip Technology Inc.

Microchip Technology Inc.

https://www.microchip.com


April 08, 2021 MX775AB1-9983 Revision 1.0 tcghelp@microchip.com

Ordering Information

Ordering Part Number	Marking Line 1	Marking Line 3	Shipping	Package
MX775ABA156M250	MX775AB	A156M250	Tube	6-Pin 7mm x 5mm LGA
MX775ABA156M250-TR	MX775AB	A156M250	Tape and Reel	6-Pin 7mm x 5mm LGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

Pin Configuration



Pin Description

Pin Number	Pin Name	Pin Type	Pin Level	Pin Function	
1	OE	I, SE	LVCMOS	Output Enable, disables to tri-state, $0 = \text{Disabled}, \ 1 = \text{Enabled}, \ 75k\Omega \text{ Pull-Up (Internal)}$	
2	NC			No connect No internal connections to the ASIC are made	
3	GND-VSS	PWR		Power Supply Ground	
4, 5	Q, /Q	O, Diff	LVPECL	Clock Output Frequency = 156.25MHz	
6	VDD	PWR		Power Supply	

Environmental Specifications


Thermal Shock	MIL-STD-883, Method 1011, Condition A
Moisture Resistance	MIL-STD-883, Method 1004
Mechanical Shock	MIL-STD-883, Method 2002, Condition C
Mechanical Vibration	MIL-STD-883, Method 2007, Condition B
Resistance to Soldering Heat	J-STD-020C, Table 5-2 Pb-free devices (except 2 cycles max)
Hazardous Substance	Pb-free / RoHS / Green Compliant
Solderability	JESD22-B102-D Method 2 (Preconditioning E)
Terminal Strength	MIL-STD-883, Method 2004, Test Condition D
Gross Leak	MIL-STD-883, Method 1014, Condition C
Fine Leak	MIL-STD-883, Method 1014, Condition A2, R1=2x10-8 atm cc/s
MSL Level	Crystal and Package MSL-1
Solvent Resistance	MIL-STD-202, Method 215


Package Information




6-Lead Low Profile Land Grid Array (LLX) - 5x7x1.22 mm Body [LLGA]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging








Microchip Technology Drawing C04-499 Rev A Sheet 1 of 2

© 2020 Microchip Technology Incorporated



6-Lead Low Profile Land Grid Array (LLX) - 5x7x1.22 mm Body [LLGA]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS					
Dimension	Limits	MIN	NOM	MAX		
Number of Terminals	N	6				
Pitch	е		2.54 BSC			
Overall Height	Α	1.08 1.15 1.22				
Standoff	A1	0.03				
Mold Cap Thickness	A3	0.85	0.90	0.95		
Overall Length	D	7.00 BSC				
Overall Width	Е	5.00 BSC				
Terminal Width	b	1.35	1.40	1.45		
Terminal Length	L	1.05	1.10	1.15		
Terminal Pullback	L1	0.10 REF				
Terminal Offset	L2	0.26 REF				

Notes:

Pin 1 visual index feature may vary, but must be located within the hatched area.
 Dimensioning and tolerancing per ASME Y14.5M
 BSC: Basic Dimension. Theoretically exact value shown without tolerances.
 REF: Reference Dimension, usually without tolerance, for information purposes only.


Microchip Technology Drawing C04-499 Rev A Sheet 2 of 2

© 2020 Microchip Technology Incorporated



6-Lead Low Profile Land Grid Array (LLX) - 5x7x1.22 mm Body [LLGA]

lote: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	MILLIMETERS			
Dimension	MIN	NOM	MAX	
Contact Pitch	E	2.54 BSC		
Contact Pad Spacing	С		3.70	
Contact Pad Width (Xnn)	Х			1.50
Contact Pad Length (Xnn)	Υ			1.30

Notes:

Dimensioning and tolerancing per ASME Y14.5M
 BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-2499 Rev A

© 2020 Microchip Technology Incorporated

Microchip makes no representations or warranties with respect to the accuracy or completeness of the information furnished in this data sheet. This information is not intended as a warranty and Microchip does not assume responsibility for its use. Microchip reserves the right to change circuitry, specifications and descriptions at any time without notice. No license, whether express, implied, arising by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Microchip's terms and conditions of sale for such products, Microchip assumes no liability whatsoever, and Microchip disclaims any express or implied warranty relating to the sale and/or use of Microchip products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right.

© 2021 Microchip Technology Inc.