# MICROCHIP

## MXT573BBA864M000

#### ±2.5ppm Stability 864MHz LVPECL TCXO

#### ClockWorks® FUSION

# **General Description**

The MXT573BBA864M000 is high stability TCXO that generates 864MHz. The output frequency is compensated to meet  $\pm 2.5$ ppm over -40°C to +85°C.

## **Applications**

- High stability reference clock
- RF and communications
- DAC or ADC reference clock

#### Absolute Maximum Ratings<sup>1</sup>

Supply Voltage (VIN)	+4.6V
Lead Temperature (soldering, 10s)	260°C
Case Temperature	115°C
Storage Temperature (T <sub>S</sub> ) ESD Machine Model	65°C to +125°C
ESD Machine Model	200V
ESD Rating (HBM)	2kV

#### **Features**

- 864MHz LVPECL
- Typical phase jitter: 0.5ps
- Guaranteed  $\pm 2.5$ ppm over -40°C to +85°C
- ±5ppm total frequency stability
- Industry standard 6-Pin 7mm x 5mm LGA package

# Operating Ratings<sup>2</sup>

Supply Voltage (VIN)	+2.375V to +3.63V
Ambient Temperature (TA)	$40^{\circ}$ C to $+85^{\circ}$ C
Junction Thermal Resistance	
LGA (T <sub>IA</sub> ) Still Air	53°C/W
` JA´	

#### **Electrical Characteristics**

VDD = 2.375 - 3.63V, TA = -40°C to +85°C, outputs terminated with 50 Ohms to VDD - 2V.3

Symbol	Parameter	Condition	Min.	Тур.	Max.	Units
IDD	Supply Current				125	mA
F0	Center Frequency			864		MHz
	Frequency Stability	Temp stability over -40°C to +85°C Total stability, note 4			±2.5 ±5	ppm
Øj	Phase Jitter			0.5		psRMS
Tstart	Start-Up Time				20	ms
TR/TF	Rise/Fall time		85		350	ps
	Duty Cycle		45		55	%
VOH	Output High Voltage	LVPECL output levels	VDD - 1.35	VDD - 1.01	VDD - 0.8	V
VOL	Output Low Voltage	LVPECL output levels	VDD - 2.0	VDD - 1.78	VDD - 1.6	V
Vswing	Peak to Peak Output Voltage Swing		0.65	0.77	0.95	V

#### Notes:

- 1. Exceeding the absolute maximum ratings may damage the device.
- 2. The device is not guaranteed to function outside its operating ratings.
- 3. Guaranteed after thermal equilibrium.
- 4. Inclusive of initial accuracy, temperature drift, aging (10yrs), shock, vibration.

ClockWorks is a registered trademark of Microchip Technology Inc.

Microchip Technology Inc.

January 04, 2019 MXT573BB1-7307 Revision 1.0 tcghelp@microchip.com


http://www.microchip.com

# **Ordering Information**

Ordering Part Number	Marking Line 2	Marking Line 4	Shipping	Package
MXT573BBA864M000	MXT573BB	A864M000	Tube	6-Pin 7mm x 5mm LGA
MXT573BBA864M000-TR	MXT573BB	A864M000	Tape and Reel	6-Pin 7mm x 5mm LGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

# **Pin Configuration**



# **Pin Description**

Pin Number	Pin Name	Pin Type	Pin Level	Pin Function
1	OE	I, SE	LVCMOS	Output Enable, disables output to tri-state, 0 = Disabled, 1 = Enabled, 50k Ohms Pull-Up (Internal)
2	DNC			Make no connection, leave floating.
3	GND	PWR		Power Supply Ground
4, 5	Q, /Q	O, Diff	LVPECL	Clock Output Frequency = 864MHz
6	VDD	PWR		Power Supply

# **Environmental Specifications**

Thermal Shock	MIL-STD-883, Method 1011, Condition A	
Moisture Resistance	MIL-STD-883, Method 1004	
Mechanical Shock	MIL-STD-883, Method 2002, Condition E	
Mechanical Vibration	MIL-STD-883, Method 2007, Condition C	
Resistance to Soldering Heat	J-STD-020C, Table 5-2 Pb-free devices (except 2 cycles max)	
Hazardous Substance	Pb-Free / RoHS / Green Compliant	
Solderability	JESD22-B102-D Method 2 (Preconditioning E)	
Terminal Strength	MIL-STD-883, Method 2004, Test Condition D	
Gross Leak	MIL-STD-883, Method 1014, Condition C	
Fine Leak	MIL-STD-883, Method 1014, Condition A2, R1=2x10-8 atm cc/s	
Solvent Resistance	MIL-STD-202, Method 215	




Figure 1. LVPECL Output 864MHz 1MHz-80MHz 300fs





Figure 2. LVPECL Output 864MHz 12kHz-20MHz 405fs

# Package Information and Recommended Land Pattern for 6-Pin LGA<sup>3</sup>



Note:

3. Package information is correct as of the publication date. For updates and most current information, go to www.microchip.com.

#### Microchip Technology Inc.

### http://www.microchip.com

Microchip makes no representations or warranties with respect to the accuracy or completeness of the information furnished in this data sheet. This information is not intended as a warranty and Microchip does not assume responsibility for its use. Microchip reserves the right to change circuitry, specifications and descriptions at any time without notice. No license, whether express, implied, arising by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Microchip's terms and conditions of sale for such products, Microchip assumes no liability whatsoever, and Microchip disclaims any express or implied warranty relating to the sale and/or use of Microchip products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right.

© 2019 Microchip Technology Inc.