# MICROCHIP

# MX574EBJ440M000

## **Ultra-Low Jitter 440MHz HCSL XO**

#### ClockWorks® FUSION

# **General Description**

The MX574EBJ440M000 is an ultra-low phase jitter XO with HCSL output optimized for high line rate applications.

#### **Features**

- 440MHz HCSL
- Typical phase noise:
  - 100fs (Integration range: 1.875MHz-20MHz)
- ±50ppm total frequency stability
- -40°C to +85°C temperature range
- Industry standard 6-Pin 7mm x 5mm LGA package

## Absolute Maximum Ratings<sup>1</sup>

Supply Voltage (VIN)	+4.6V
Lead Temperature (soldering, 10s)	260°C
Case Temperature	115°C
Storage Temperature (T <sub>S</sub> ) ESD Machine Model	65°C to +125°C
ESD Machine Model	200V
ESD Rating (HBM)	2kV

# Operating Ratings<sup>2</sup>

Supply Voltage (VIN)	+2.375V to +3.63V
Ambient Temperature (TA)	40°C to $+85$ °C
Junction Thermal Resistance	
LGA (T <sub>IC</sub> ) Still Air	53°C/W
` JC ′	

## **Electrical Characteristics**

VDD =  $2.5V \pm 5\%$  or  $3.3V \pm 10\%$ ,  $-40^{\circ}$ C to  $+85^{\circ}$ C, outputs terminated with 50 Ohms to VSS.<sup>3</sup>

Symbol	Parameter	Condition	Min.	Typ.	Max.	Units
IDD	Supply Current			95	120	mA
F0	Center Frequency			440		MHz
	Frequency Stability	Note 4			±50	ppm
Øj	Phase Noise	Integration Range (12kHz to 20MHz) Integration Range (1.875MHz to 20MHz)		137 100		fsRMS
Tstart	Start-Up Time				10	ms
TR/TF	Rise/Fall time	20%-80%	150	300	450	ps
	Duty Cycle		48	50	52	%
VOH	Output High Voltage	HCSL output levels	660	700	850	mV
VOL	Output Low Voltage	HCSL output levels	-150	0	27	mV
VOVS	Max Output Including Overshoot				VOH + 0.3	V
VUDS	Min Output Including Undershoot		VOL - 0.3			V
VRB	Ringback Voltage		0.2			V
VOX	Absolute Crossing Point		250	350	550	mV
Vswing	Peak to Peak Output Voltage Swing		640	700	950	mV

#### **Notes:**

- $1. \ Exceeding \ the \ absolute \ maximum \ ratings \ may \ damage \ the \ device.$
- 2. The device is not guaranteed to function outside its operating ratings.
- 3. Guaranteed after thermal equilibrium.
- 4. Inclusive of initial accuracy, temperature drift, aging, shock, vibration.

ClockWorks is a registered trademark of Microchip Technology Inc.

Microchip Technology Inc.

http://www.microchip.com


September 14, 2020 MX574EB1-5326 Revision 1.0 tcghelp@microchip.com

# **Ordering Information**

<b>Ordering Part Number</b>	Marking Line 1	Marking Line 3	Shipping	Package
MX574EBJ440M000	MX574EB	J440M000	Tube	6-Pin 7mm x 5mm LGA
MX574EBJ440M000-TR	MX574EB	J440M000	Tape and Reel	6-Pin 7mm x 5mm LGA

Devices are Green and RoHS compliant. Sample material may have only a partial top mark.

# **Pin Configuration**



# **Pin Description**

Pin Number	Pin Name	Pin Type	Pin Level	Pin Function
1	OE	I, SE	LVCMOS	Output Enable, disables output to tri-state, 1 = Disabled, 0 = Enabled, 50k Ohms Pull-Down (Internal)
2	DNC			Make no connection, leave floating.
3	GND	PWR		Power Supply Ground
4, 5	Q, /Q	O, Diff	HCSL	Clock Output Frequency = 440MHz
6	VDD	PWR		Power Supply

# **Environmental Specifications**

Thermal Shock	MIL-STD-883, Method 1011, Condition A	
Moisture Resistance	MIL-STD-883, Method 1004	
Mechanical Shock	MIL-STD-883, Method 2002, Condition C	
Mechanical Vibration	MIL-STD-883, Method 2007, Condition A	
Resistance to Soldering Heat	J-STD-020C, Table 5-2 Pb-free devices (except 2 cycles max)	
Hazardous Substance	Pb-Free / RoHS / Green Compliant	
Solderability	JESD22-B102-D Method 2 (Preconditioning E)	
Terminal Strength	MIL-STD-883, Method 2004, Test Condition D	
Gross Leak	MIL-STD-883, Method 1014, Condition C	
Fine Leak	MIL-STD-883, Method 1014, Condition A2, R1=2x10-8 atm cc/s	
MSL Level	Crystal - MSL-1, Package MSL-3	
Solvent Resistance	MIL-STD-202, Method 215	

Microchip Technology Inc. MX574EBJ440M000





Figure 1. HCSL Output 440MHz 12kHz-20MHz 137fs

# Package Information and Recommended Land Pattern for 6-Pin LGA<sup>3</sup>



Note:

3. Package information is correct as of the publication date. For updates and most current information, go to www.microchip.com.

## Microchip Technology Inc.

## http://www.microchip.com

Microchip makes no representations or warranties with respect to the accuracy or completeness of the information furnished in this data sheet. This information is not intended as a warranty and Microchip does not assume responsibility for its use. Microchip reserves the right to change circuitry, specifications and descriptions at any time without notice. No license, whether express, implied, arising by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Microchip's terms and conditions of sale for such products, Microchip assumes no liability whatsoever, and Microchip disclaims any express or implied warranty relating to the sale and/or use of Microchip products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right.

© 2020 Microchip Technology Inc.